HITPOINT TEL:8862-26013311 FAX:8862-26013898

NO.4 Lane 505, Zhongzheng Rd,. Linkou Shiang, Taipei, Taiwan 24445 . R.O.C

Piezo Siren

PS-551DGQ

(ROHS)


DATE:2012-3-8

1 . Electrical Characteristics

VER .:0

Resonant Frequency (KHz)	2.8 ±0.5	
Operating Voltage (Vdc)	5 ~ 15	
Rated Voltage (Vdc)	12	
Current Consumption (mA/max.)	200 at Rated Voltage	
Sound Pressure Level (dB/min.)	105 at 100cm at Rated Voltage	
Tone/Pulse Rate (Hz)	Pulse 1.2 ±20%	
LED Colour	GREEN	
Operating Temperature (°C)	-20 ~ +70	
Storage Temperature (°C)	-30 ~ +80	

2 . Dimensions and Material 2-1 Shape



NO.4 Lane 505, Zhongzheng Rd,. Linkou Shiang, Taipei, Taiwan 24445 . R.O.C

2-2 Material

Housing	ABS 757 UL94HB plastic resin (Color : Black)
Leading Wire	20 AWG
Weight (Gram)	78


3. TESTING METHOD


· Standard Measurement conditions

Temperature: $25\pm 2^{\circ}C$ Humidity: 45-60%

· Acoustic Characteristics

The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below.





4. RELIABILITY

ITEMS	METHOD OF TEST AND MEASUREMENTS	PERFORMANCE
Coldness	After 98 hours of being exposed to -30 ${}^{\circ}\!\!{}^{\circ}\!\!{}^{\circ}$	No abnormality
withstanding	environment, should be returned to normal	shall exist
	environment for 2 hours, then re-proceed to test.	
Hotness	After 98 hours of being exposed to +80 ${}^\circ\!{C}$	No abnormality
withstanding	environment, should be returned to normal	shall exist
	environment for 2 hours, then re-proceed to test.	
Humidity	After 98 hours of being exposed to 40 $^{\circ}\!\!{\mathcal C}$ 95%RH	No abnormality
withstanding	environment in actual operation, should be	shall exist
	returned to normal environment for 2 hours, then	
	re-proceed to test.	
Durability	10sec on/10sec off ; 1000hours(180000 cycles)	No abnormality
		shall exist
Vibration	Linear vibrate frequency rate: 5~55Hz	No abnormality
withstanding	Time:180sec , applied in X, Y and Z directions for	shall exist
	3 times each.	

5. PACKAGE METHOD

- <1> One inner box consists of 1pcs.
- <2> 180pcs of PS-551DQ are packed in a carton box. (L*W*H=520*335*290mm)
- <3> N . W . : : 14KGS ; G . W . : 16KGS ;
- <4> RoHS Mark